



A detailed technical cutaway drawing of a microscope objective. The drawing shows the internal optical elements, including the objective lens and eyepiece lens, mounted within a complex metal housing. The objective is shown in a cross-section view, revealing the internal structure and the mounting of the lens elements. The drawing is rendered in a clean, technical style with black lines and shading to indicate depth and form.

Port / Conexión	Function / Función	Thread / Rosca
1	From the compressor / Proveniente del compresor	M22x1,5
21	To the reservoirs / A los calderines	M22x1,5
22	To the regenerated air reservoir / Al calderín de regeneración	M16x1,5 VOSS
4/23	Control port / Puerto de control	Closed / Taponada
3	Exhaust for compressed air / Escape de aire comprimido	-
6	Heating / Calentador	Bayonet DIN 72585 A1-2.1

Installation / Instalación: Exhaust (3) must look down. / El escape de aire (3) debe estar orientado hacia abajo.

Modification	4					Drawn		
	3					18/06/14 A.U.		
	2					Checked		
	1					18/06/14 A.L.		
	nº	Modified	Date	Reason	General Tolerance	Assembly	-	
Comments				-	Part name	Air Dryer / Secador de aire		
				Material	ID. Reference	2310635		
				-	Scale: -		Sheet 1/2	
					Review: 0			



Modification	4				Drawn				
	3				18/06/14 A.U.				
	2				Checked				
	1				18/06/14 A.L.				
	nº	Modified	Date	Reason	General Tolerance	Assembly	-		
Comments					ISO 2768 c-K	Part name	Air Dryer / Secador de aire		
					Material	ID. Reference	2310635		
					-	Scale: 1/2			Sheet 2/2
						Review: 0			